

Workplace design

Spray Booth

Spray booth L=1000 mm. Varenr. 01-800

With light, Andraee-filter, wheels and drip tray.
Galvanized steel.

Recommended air flow: 2.000 m³/h, duct connection \varnothing 250 mm in left-, right side and top.
The spray booth connects to 230V.
H: 2035 mm W: 1000 mm D: 1000 mm

Spray booth L=1400 mm. Varenr. 01-801

With light, Andraee-filter, wheels and drip tray.
Galvanized steel.


Recommended air flow: 2.000 m³/h, duct connection \varnothing 250 mm in left-, right side and top.
The spray booth connects to 230V.
H: 2035 mm W: 1400 mm D: 1000 mm

Spray booth L=1800 mm. Varenr. 01-802

With light, Andraee-filter, wheels and drip tray.
Galvanized steel.

Recommended air flow: 3.600 m³/h, duct connection 2 x \varnothing 200 mm in left-, right side and top.
The spray booth connects to 230V.
H: 2035 mm W: 1800 mm D: 1000 mm

Dimensions



Spray booth for smaller items

Ordering table

Art. No.	Description
01-800	Spray booth B=1000 mm.
01-801	Spray booth B=1400 mm.
01-802	Spray booth B=1800 mm.
15-040	Andraee-filter